


AUTOMATED COMPLETE SYSTEM
DL2000


THROUGHFEED VIBRATORS
DL



Misprints, mistakes and construction deviations reserved.


www.bn-medienagentur.de

Throughfeed vibrators DL - eng - 05 - 2023



Deburring · Edge rounding
Cleaning · Degreasing

Compact, space-saving machine design with multiple spirally arranged working tub. Ideal to treat different parts in a continuous process. Gentle and low-contact treatment thanks to timed addition of parts.



THROUGHFEED VIBRATORS DL



Technical data:

- Space-saving design with high rate of production
- Tub lining made of wear-resistant polyurethane
- Continuous return of processing media on two or three levels
- Integrated separation unit to separate media and parts as well as to remove undersize media (undersize separation)

Optional features:

- Additional separation zone for the separation of parts and media
- Sound protection cabin to encase the whole production unit
- Integration into a complete production line including feeding and discharge, cleaning as well as drying of the parts

Technical data:

Description		DL600	DL1000	DL2000
Working tub volume	l	340	1000	2000
Length of processing zone	m	11	18	14
Levels of processing zone		3	3	2
Operating voltage	V Hz	400 50	400 50	400 50
Drive power	kW	3,0	12,4	12,4
Empty weight basic machine	kg	2000	3700	4400
Operating weight max.	kg	3000	5500	7000
Space requirement	m ²	3	7	10

Dimensions in mm:

Description		DL600	DL1000	DL2000
Width throughfeed vibrator incl. separation unit	A	2060	2690	3620
Width discharge	B	350	390	540
Length throughfeed vibrator incl. separation unit	C	1850	2600	2970
Diameter throughfeed vibrator	D	1480	2325	2830
Width working tub	E	240	255	395
Bottom edge discharge	F	1200	1710	1770
Top edge throughfeed vibrator	G	1680	2105	2280
Width entry	H	300	360	560
Bottom edge entry	I	835	860	1220

